



PRODUCT-DETAILS

3GAA098102-AHE

No Description Available

"No longer for sale" replaced by 3GAA098508-

General Information

Product ID	3GAA098102-AHE
ABB Type Designation	M3AA 90L 2-4 v Dh
Catalog Description	No Description Available

Ordering

ABB Type Designation	M3AA 90L 2-4 v Dh
Product Name	3-Phase squirrel cage motor
Product Type	3AA2 M3AA IE2 AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Spain (ES) Sweden (SE) Poland (PL)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA098102-AHA

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
YY	--	50 Hz	400-415 V	2.20 kW	2860 r/min	4.60 A	0.880	0.00 %	7.35 N·m	0.00
Y	--	50 Hz	400-415 V	0.45 kW	1460 r/min	1.40 A	0.650	0.00 %	2.94 N·m	0.00

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	Yes
Type of Duty	S1

Voltage Code H

Mechanical

Frame Material	Aluminum
Frame Size	90
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
Lubrication	For life
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	16 kg
Gross Weight	16.48 kg

Classifications

Standards	IEC 60034-1
UNSPSC	26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → Legacy IEC Low Voltage Motors → Aluminum Motors
Motors and Generators → IEC Low Voltage AC Motors → Legacy IEC Low Voltage Motors → Global Motors
Motors and Generators → IEC Low Voltage AC Motors → Marine Motors → Marine Process Performance Motors