


PRODUCT-DETAILS

3GAA094540-BRE
(3GAA094540-BRE)



General Information

Product ID	3GAA094540-BRE
ABB Type Designation	M3AA 90LD 8
Catalog Description	(3GAA094540-BRE)

Ordering

ABB Type Designation	M3AA 90LD 8
Invoice Description	M3AA 90LD 8
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015220

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	60 Hz	380 V	0.75 kW	815 r/min	2.50 A	0.620
Temperature Class Default							--
Altitude							1000 m
Ambient Temperature							40 °C
IC Class							IC411
IP Class							IP55
Insulation Class							ICLF
Direction of Rotation							Both sides
Number of Poles (High)							6
Two Speed Motor							No
Type of Duty							S1
Voltage Code							R

Mechanical

Frame Material	Aluminum
Frame Size	90
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	18 kg
Gross Weight	21 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

