


PRODUCT-DETAILS

# 3GAA098509-AHF

## (3GAA098509-AHF)



### General Information

Product ID	3GAA098509-AHF
ABB Type Designation	M3AA 90L 4-8
Catalog Description	(3GAA098509-AHF)

### Ordering

ABB Type Designation	M3AA 90L 4-8
Invoice Description	M3AA 90L 4-8
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA098105-AHE

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
YY	--	50 Hz	415 V	1.70 kW	1402 r/min	4.00 A	0.790	74.80 %	11.60 N·m	4.70
Y	--	50 Hz	415 V	0.35 kW	707 r/min	1.60 A	0.540	57.30 %	4.70 N·m	2.60

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class NA Full Load (100%) 57.3 % Partial Load (75%) 52.4 % Partial Load (50%) 45.0 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	Yes
Type of Duty	S1
Voltage Code	H

Mechanical

Frame Material	Aluminum
Frame Size	90
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	16 kg
Gross Weight	19 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

---

## Categories

---

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

