

PRODUCT-DETAILS

3GAA101530-ADK

IE3 Premium Efficiency Aluminum Motors, 3 kW, 400 V (3GAA101530-ADK)



General Information	
Product ID	3GAA101530-ADK
ABB Type Designation	M3AA 100LC 2
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 3 kW, 400 V (3GAA101530-ADK)

Ordering	
ABB Type Designation	M3AA 100LC 2
Invoice Description	M3AA 100LC 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA3_M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Romania (RO) Poland (PL)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany
Medium Description	3kW, 2 Poles, Frame Size 100, 3 Phases, 400V, 50Hz, IP55 Enclosure,

IMB3/IM1001 Mounting (3GAA101530-ADK)	
Short Description	3kW, 2P, Frame Size 100, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	3.00 kW	2896 r/min	3.10 A	0.900	87.10 %	9.80 N·m	8.40
D	--	50 Hz	400 V	3.00 kW	2896 r/min	5.40 A	0.900	87.10 %	9.80 N·m	8.40
Y	--	50 Hz	660 V	3.00 kW	2877 r/min	3.30 A	0.920	87.10 %	9.90 N·m	7.60
D	--	50 Hz	380 V	3.00 kW	2877 r/min	5.70 A	0.920	87.10 %	9.90 N·m	7.60
D	--	50 Hz	415 V	3.00 kW	2906 r/min	5.20 A	0.900	87.10 %	9.80 N·m	9.00
D	--	60 Hz	460 V	3.00 kW	3512 r/min	4.70 A	0.890	88.50 %	8.10 N·m	9.90

Connection Configuration	D
Temperature Class Default	--
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	3 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 87.1 % Partial Load (75%) 87.9 % Partial Load (50%) 87.3 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 88.5 % Partial Load (75%) 88.7 % Partial Load (50%) 87.3 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Aluminum
Frame Size	100
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions	
Package Level 1 Units	0 carton
Product Net Depth / Length	432 mm
Product Net Height	237 mm
Product Net Width	200 mm
Product Net Weight	28 kg
Gross Weight	33 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories	
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors	

