



PRODUCT-DETAILS

3GAA102550-JSK

IE3 Premium Efficiency Aluminum Motors, 2.2 kW, 400 V (3GAA102550-JSK)



General Information

Product ID	3GAA102550-JSK
ABB Type Designation	M3AA 100LE 4
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 2.2 kW, 400 V (3GAA102550-JSK)

Ordering

ABB Type Designation	M3AA 100LE 4
Invoice Description	M3AA 100LE 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA3_M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL) Romania (RO)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany
Medium Description	2.2kW, 4 Poles, Frame Size 100, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB34/IM2101 Mounting (3GAA102550-JSK)
Short Description	2.2kW, 4P, Frame Size 100, 3PH, 400V, 50Hz, IP55, IMB34/IM2101

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	2.20 kW	1454 r/min	4.30 A	0.830	86.70 %	14.50 N·m	8.90
D	--	50 Hz	230 V	2.20 kW	1454 r/min	7.40 A	0.830	86.70 %	14.50 N·m	8.90
Y	--	50 Hz	380 V	2.20 kW	1448 r/min	4.40 A	0.840	86.70 %	14.50 N·m	8.10
D	--	50 Hz	220 V	2.20 kW	1448 r/min	7.60 A	0.840	86.70 %	14.50 N·m	8.10
Y	--	50 Hz	415 V	2.20 kW	1458 r/min	4.10 A	0.810	86.70 %	14.50 N·m	9.50
Y	--	60 Hz	460 V	2.20 kW	1760 r/min	3.80 A	0.810	89.50 %	11.90 N·m	10.20

Connection Configuration	Y
Temperature Class	--
Default	
Input Voltage (U <sub>in</sub> )	400 V
Frequency (f)	50 Hz
Output Power	2.2 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 86.7 % Partial Load (75%) 87.0 % Partial Load (50%) 85.5 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 89.5 % Partial Load (75%) 89.2 % Partial Load (50%) 87.4 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	100
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB34 IM2101
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	432 mm
Product Net Height	237 mm
Product Net Width	200 mm
Product Net Weight	36 kg
Gross Weight	41 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

SCIP

27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC

26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

