




PRODUCT-DETAILS

3GAA103530-BDE

IE2 High Efficiency Aluminum Motors, 1.5 kW,  
400 V (3GAA103530-BDE)



General Information

Product ID	3GAA103530-BDE
ABB Type Designation	M3AA 100LC 6
Catalog Description	IE2 High Efficiency Aluminum Motors, 1.5 kW, 400 V (3GAA103530-BDE)

Ordering

ABB Type Designation	M3AA 100LC 6
Invoice Description	M3AA 100LC 6
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Romania (RO) Finland (FI) China (CN) Poland (PL)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA103312-BDE 3GAA103442-BDE
Stocked At (Warehouses)	Menden, Germany Sant Quirze del Vallés - BCN, Spain Shanghai, China

Medium Description	1.5kW, 6 Poles, Frame Size 100, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAA103530-BDE)
Short Description	1.5kW, 6P, Frame Size 100, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	1.50 kW	945 r/min	2.10 A	0.730	80.30 %	15.10 N·m	3.90
D	--	50 Hz	400 V	1.50 kW	945 r/min	3.60 A	0.730	80.30 %	15.10 N·m	3.90
D	--	60 Hz	460 V	1.50 kW	1150 r/min	3.20 A	0.700	83.30 %	12.40 N·m	4.40

Connection Configuration	D
Temperature Class Default	--
Input Voltage (U <sub>in</sub> )	400 V
Frequency (f)	50 Hz
Output Power	1.5 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 80.3 % Partial Load (75%) 81.4 % Partial Load (50%) 80.7 %
IE Class Data (60 Hz)	IE Class IE1 Full Load (100%) 83.3 % Partial Load (75%) 83.3 % Partial Load (50%) 81.4 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Aluminum
Frame Size	100
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	351 mm
Product Net Height	237 mm
Product Net Width	200 mm
Product Net Weight	26 kg
Gross Weight	31 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)
Classifications	
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

