


PRODUCT-DETAILS

3GAA104520-CSK

IE3 Premium Efficiency Aluminum Motors, 0.75 kW, 400 V (3GAA104520-CSK)



General Information	
Product ID	3GAA104520-CSK
ABB Type Designation	M3AA 100LB 8
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 0.75 kW, 400 V (3GAA104520-CSK)

Ordering	
ABB Type Designation	M3AA 100LB 8
Invoice Description	M3AA 100LB 8
Product Name	3-Phase squirrel cage motor
Product Type	3AA3_M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) China (CN) Poland (PL)
Customs Tariff Number	85015100
Medium Description	0.75kW, 8 Poles, Frame Size 100, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB14/IM3601 Mounting (3GAA104520-CSK)
Short Description	0.75kW, 8P, Frame Size 100, 3PH, 400V, 50Hz, IP55, IMB14/IM3601

Electrical

Electrical Data										
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	0.75 kW	710 r/min	2.13 A	0.650	75.00 %	10.00 N·m	4.40
D	--	50 Hz	230 V	0.75 kW	710 r/min	3.70 A	0.650	75.00 %	10.00 N·m	4.40
Y	--	50 Hz	380 V	0.75 kW	705 r/min	2.13 A	0.690	75.00 %	10.10 N·m	4.20
D	--	50 Hz	220 V	0.75 kW	705 r/min	3.70 A	0.690	75.00 %	10.10 N·m	4.20
Y	--	50 Hz	415 V	0.75 kW	713 r/min	2.16 A	0.620	75.00 %	10.00 N·m	4.50
Y	--	60 Hz	460 V	0.75 kW	866 r/min	1.93 A	0.610	75.50 %	8.27 N·m	4.90
Connection Configuration										Y
Temperature Class Default										--
Input Voltage (U _{in})										400 V
Frequency (f)										50 Hz
Output Power										0.75 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 75.0 % Partial Load (75%) 74.0 % Partial Load (50%) 69.4 %
IE Class Data (60 Hz)										IE Class IE3 Full Load (100%) 75.5 % Partial Load (75%) 73.9 % Partial Load (50%) 68.5 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										8
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Material	Aluminum
Frame Size	100
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB14 IM3601
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	432 mm
Product Net Height	237 mm
Product Net Width	200 mm

Product Net Weight	25 kg
Gross Weight	30 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

