



PRODUCT-DETAILS

3GAA103002-BSESK2

No Description Available

"No longer for sale" replaced by 3GAA103002-

General Information	
Product ID	3GAA103002-BSESK2
ABB Type Designation	M3AA 100 LC-6 HO
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M3AA 100 LC-6 HO
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
Country of Origin	Romania (RO)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	tE
Y	--	50 Hz	380 V	2.20 kW	930 r/min	5.80 A	0.750	0.00 %	22.35 N·m	0.00	
Y	--	50 Hz	400 V	2.20 kW	940 r/min	5.70 A	0.710	0.00 %	22.35 N·m	0.00	
Y	--	50 Hz	415 V	2.20 kW	940 r/min	5.90 A	0.670	77.70 %	21.13 N·m	0.00	
Y	--	60 Hz	380 V	2.20 kW	1115 r/min	5.30 A	0.790	0.00 %	21.13 N·m	0.00	0
D	--	60 Hz	220 V	2.20 kW	1115 r/min	9.00 A	0.790	0.00 %	0.00 N·m	0.00	0
Y	--	60 Hz	460 V	2.20 kW	1145 r/min	5.00 A	0.680	0.00 %	0.00 N·m	0.00	0

Frame Size	100
Gross Weight	26.65 kg
IC Class	IC411
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55W
Lubrication	For life

Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Package Level 1 Units	1 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	26 kg
Product Type	3AA2__M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA103002-BSESK3
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S