



PRODUCT-DETAILS

# 3GAA104520-ADE

## IE2 High Efficiency Aluminum Motors, 1.1 kW, 400 V (3GAA104520-ADE)



General Information	
Product ID	3GAA104520-ADE
ABB Type Designation	M3AA 100LB 8
Catalog Description	IE2 High Efficiency Aluminum Motors, 1.1 kW, 400 V (3GAA104520-ADE)

Ordering	
ABB Type Designation	M3AA 100LB 8
Invoice Description	M3AA 100LB 8
Product Name	3-Phase squirrel cage motor
Product Type	3AA2__M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) China (CN) Poland (PL)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA104062-ADA 3GAA104002-ADE 3GAA104442-ADE

Stocked At (Warehouses)	Shanghai, China
Medium Description	1.1kW, 8 Poles, Frame Size 100, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA104520-ADE)
Short Description	1.1kW, 8P, Frame Size 100, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	1.10 kW	695 r/min	1.83 A	0.660	76.00 %	15.10 N-m	3.40
D	--	50 Hz	400 V	1.10 kW	695 r/min	3.10 A	0.660	76.00 %	15.10 N-m	3.40
D	--	60 Hz	460 V	1.10 kW	860 r/min	3.10 A	0.570	77.40 %	12.20 N-m	4.00
Connection Configuration										D
Temperature Class Default										--
Input Voltage (U <sub>in</sub> )										400 V
Frequency (f)										50 Hz
Output Power										1.1 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2 Full Load (100%) 76.0 % Partial Load (75%) 74.9 % Partial Load (50%) 68.2 %
IE Class Data (60 Hz)										IE Class IE2 Full Load (100%) 77.4 % Partial Load (75%) 75.9 % Partial Load (50%) 71.0 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										8
Two Speed Motor										No
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Aluminum
Frame Size	100
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	351 mm

Product Net Height	237 mm
Product Net Width	200 mm
Product Net Weight	23 kg
Gross Weight	28 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

