



PRODUCT-DETAILS

3GAA112102-ADE

No Description Available

"No longer for sale" replaced by 3GAA112360-

General Information

Product ID	3GAA112102-ADE
ABB Type Designation	M3AA 112MB 4 HO
Catalog Description	No Description Available

Additional Information

ABB Type Designation	M3AA 112MB 4 HO
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
Country of Origin	Poland (PL) Sweden (SE) Romania (RO)
Customs Tariff Number	85015220
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	5.50 kW	1410 r/min	6.80 A	0.810	82.50 %	36.90 N·m	6.20
D	--	50 Hz	400 V	5.50 kW	1410 r/min	11.80 A	0.810	82.50 %	36.90 N·m	6.20
D	--	60 Hz	460 V	5.50 kW	1730 r/min	10.20 A	0.780	86.20 %	30.50 N·m	7.40

Frame Material	Aluminum
Frame Size	112
Gross Weight	34.65 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE1 Full Load (100%) 85.1 % Partial Load (75%) 86.9 % Partial Load (50%) 86.3 %
IE Class Data (60 Hz)	IE Class IE1 Full Load (100%) 88.1 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4

Package Level 1 Units	1 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	34 kg
Product Type	3AA1_M3AA_IE1_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA112360-ADE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D