




PRODUCT-DETAILS

3GAA112320-BEE

IE2 High Efficiency Aluminum Motors, 4 kW, 500 V (3GAA112320-BEE)



General Information	
Product ID	3GAA112320-BEE
ABB Type Designation	M3AA 112MB 4
Catalog Description	IE2 High Efficiency Aluminum Motors, 4 kW, 500 V (3GAA112320-BEE)

Ordering	
ABB Type Designation	M3AA 112MB 4
Invoice Description	M3AA 112MB 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA2__M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) China (CN) Poland (PL)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA112312-BEE
Stocked At	Shanghai, China

(Warehouses)	
Medium Description	4kW, 4 Poles, Frame Size 112, 3 Phases, 500V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAA112320-BEE)
Short Description	4kW, 4P, Frame Size 112, 3PH, 500V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data											
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	
D	--	50 Hz	500 V	4.00 kW	1445 r/min	7.10 A	0.750	86.70 %	26.40 N·m	7.30	
D	--	60 Hz	575 V	4.00 kW	1745 r/min	5.90 A	0.770	87.60 %	21.80 N·m	8.20	
Connection Configuration										D	
Temperature Class Default										--	
Input Voltage (U _{in})										500 V	
Frequency (f)										50 Hz	
Output Power										4 kW	
Altitude										1000 m	
Ambient Temperature										40 °C	
IC Class										IC411	
IE Class Data (50 Hz)										IE Class IE2 Full Load (100%) 86.7 % Partial Load (75%) 86.5 % Partial Load (50%) 85.2 %	
IE Class Data (60 Hz)										IE Class IE2 Full Load (100%) 87.6 % Partial Load (75%) 87.5 % Partial Load (50%) 85.7 %	
IP Class										IP55	
Insulation Class										ICLF	
Direction of Rotation										Both sides	
Number of Poles (High)										4	
Two Speed Motor										No	
Type of Duty										S1	
Voltage Code										E	

Mechanical

Frame Material	Aluminum
Frame Size	112
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	393 mm
Product Net Height	249 mm

Product Net Width	230 mm
Product Net Weight	34 kg
Gross Weight	39 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories	
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors	

