



PRODUCT-DETAILS

3GAA108218-ADE

No Description Available

"No longer for sale" replaced by 3GAA109522-

General Information

Product ID	3GAA108218-ADE
ABB Type Designation	M3AA 100LB 4-8 pc
Catalog Description	No Description Available

Ordering

ABB Type Designation	M3AA 100LB 4-8 pc
Product Name	3-Phase squirrel cage motor
Product Type	3AA2 M3AA IE2 AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Spain (ES) Sweden (SE)
Customs Tariff Number	85015100
Replaced Product ID (OLD)	3GAA108218-ADA

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	380-400 V	1.50 kW	1440 r/min	3.70 A	0.820	0.00 %	9.95 N·m	0.00
Y	--	50 Hz	380-400 V	0.75 kW	700 r/min	2.90 A	0.600	0.00 %	10.23 N·m	0.00

Temperature Class Default	--
IC Class	IC411
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	8
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Aluminum
Frame Size	100
Lubrication	For life
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	20 kg
Gross Weight	20.65 kg

Classifications

Standards	IEC 60034-1
UNSPSC	26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → Legacy IEC Low Voltage Motors → Aluminum Motors
Motors and Generators → IEC Low Voltage AC Motors → Legacy IEC Low Voltage Motors → Global Motors
Motors and Generators → IEC Low Voltage AC Motors → Marine Motors → Marine Process Performance Motors