



PRODUCT-DETAILS

3GAA113312-CDE

No Description Available

"No longer for sale" replaced by 3GAA113320-

General Information

Product ID	3GAA113312-CDE
ABB Type Designation	M3AA 112MB 6
Catalog Description	No Description Available

Additional Information

ABB Type Designation	M3AA 112MB 6
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
Country of Origin	Spain (ES) Sweden (SE) Poland (PL)
Customs Tariff Number	85015220
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	2.20 kW	955 r/min	3.00 A	0.720	81.90 %	22.00 N·m	5.20
D	--	50 Hz	400 V	2.20 kW	955 r/min	5.30 A	0.720	81.90 %	22.00 N·m	5.20
D	--	60 Hz	460 V	2.20 kW	1160 r/min	5.00 A	0.650	84.40 %	18.10 N·m	5.90

Frame Material	Aluminum
Frame Size	112
Gross Weight	28.67 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 81.9 % Partial Load (75%) 82.3 % Partial Load (50%) 79.8 %
IE Class Data (60 Hz)	IE Class IE1 Full Load (100%) 84.4 %
IM Class	IMB14 IM3601
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	0 carton

Product Name	3-Phase squirrel cage motor
Product Net Weight	28 kg
Product Type	3AA2_M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA113320-CDE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D