




PRODUCT-DETAILS

3GAA113330-JDK

IE3 Premium Efficiency Aluminum Motors, 2.2 kW, 400 V (3GAA113330-JDK)



General Information	
Product ID	3GAA113330-JDK
ABB Type Designation	M3AA 112MC 6
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 2.2 kW, 400 V (3GAA113330-JDK)

Ordering	
ABB Type Designation	M3AA 112MC 6
Invoice Description	M3AA 112MC 6
Product Name	3-Phase squirrel cage motor
Product Type	3AA3__M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015220
Medium Description	2.2kW, 6 Poles, Frame Size 112, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB34/IM2101 Mounting (3GAA113330-JDK)
Short Description	2.2kW, 6P, Frame Size 112, 3PH, 400V, 50Hz, IP55, IMB34/IM2101

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	2.20 kW	967 r/min	3.00 A	0.690	84.30 %	21.70 N·m	6.50
D	--	50 Hz	400 V	2.20 kW	967 r/min	5.20 A	0.690	84.30 %	21.70 N·m	6.50
Y	--	50 Hz	660 V	2.20 kW	962 r/min	3.00 A	0.720	84.30 %	21.80 N·m	6.00
D	--	50 Hz	380 V	2.20 kW	962 r/min	5.30 A	0.720	84.30 %	21.80 N·m	6.00
D	--	50 Hz	415 V	2.20 kW	970 r/min	5.20 A	0.660	84.30 %	21.60 N·m	6.90
D	--	60 Hz	460 V	2.20 kW	1172 r/min	4.60 A	0.660	89.50 %	17.90 N·m	7.30

Connection Configuration	D
Temperature Class Default	--
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	2.2 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 84.3 % Partial Load (75%) 84.7 % Partial Load (50%) 83.2 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 89.5 % Partial Load (75%) 89.6 % Partial Load (50%) 88.4 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Aluminum
Frame Size	112
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB34 IM2101
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	431 mm
Product Net Height	260 mm
Product Net Width	222 mm
Product Net Weight	43 kg
Gross Weight	48 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories	
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors	

