

PRODUCT-DETAILS

# 3GAA131120-AGE

## (3GAA131120-AGE)



General Information	
Product ID	3GAA131120-AGE
ABB Type Designation	M3AA 132SB 2
Catalog Description	(3GAA131120-AGE)

Ordering	
ABB Type Designation	M3AA 132SB 2
Invoice Description	M3AA 132SB 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA2__M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA131442-AGE

Electrical

Electrical Data										
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	IS/IN	
Y	--	50 Hz	415 V	5.50 kW	2920 r/min	10.30 A	0.840	88.00 %	8.80	
Temperature Class Default										--
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2 Full Load (100%) 88.0 % Partial Load (75%) 87.8 % Partial Load (50%) 86.0 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										2
Two Speed Motor										No
Type of Duty										S1
Voltage Code										G

Mechanical										
Frame Material										Aluminum
Frame Size										132
Bearing										6208-2Z/C3
Bearing NDE										6206-2Z/C3
IM Class										IMB3 IM1001
Terminator Box Location										D-End top

Dimensions										
Package Level 1 Units										0 carton
Product Net Weight										52 kg
Gross Weight										57 kg

Environmental										
WEEE Category										5. Small Equipment (No External Dimension More Than 50 cm)
SCIP										27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications										
UNSPSC										26101100

---

## Categories

---

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

