




PRODUCT-DETAILS

3GAA111330-ADK

IE3 Premium Efficiency Aluminum Motors, 5.5 kW, 400 V (3GAA111330-ADK)



General Information

Product ID	3GAA111330-ADK
ABB Type Designation	M3AA 112MC 2
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 5.5 kW, 400 V (3GAA111330-ADK)

Ordering

ABB Type Designation	M3AA 112MC 2
Invoice Description	M3AA 112MC 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA3_M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Romania (RO) Poland (PL)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany
Medium Description	5.5kW, 2 Poles, Frame Size 112, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA111330-ADK)
Short Description	5.5kW, 2P, Frame Size 112, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	5.50 kW	2909 r/min	5.58 A	0.910	89.20 %	18.08 N·m	8.60
D	--	50 Hz	400 V	5.50 kW	2909 r/min	9.67 A	0.910	89.20 %	18.08 N·m	8.60
Y	--	50 Hz	660 V	5.50 kW	2900 r/min	5.79 A	0.920	90.30 %	18.16 N·m	8.80
D	--	50 Hz	380 V	5.50 kW	2899 r/min	10.10 A	0.920	90.30 %	18.16 N·m	8.20
D	--	50 Hz	415 V	5.50 kW	2915 r/min	9.34 A	0.900	89.20 %	18.08 N·m	9.20
D	--	60 Hz	460 V	5.50 kW	3523 r/min	8.40 A	0.890	89.50 %	15.00 N·m	11.20

Connection Configuration	D
Temperature Class	--
Default	
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	5.5 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 89.2 % Partial Load (75%) 89.8 % Partial Load (50%) 89.2 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 89.5 % Partial Load (75%) 88.1 % Partial Load (50%) 87.1 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Aluminum
Frame Size	112
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	431 mm
Product Net Height	260 mm
Product Net Width	222 mm
Product Net Weight	48 kg
Gross Weight	53 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

SCIP27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

