


PRODUCT-DETAILS

3GAA131130-HEK

IE3 Premium Efficiency Aluminum Motors, 7.5 kW, 500 V (3GAA131130-HEK)



General Information	
Product ID	3GAA131130-HEK
ABB Type Designation	M3AA 132SC 2
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 7.5 kW, 500 V (3GAA131130-HEK)

Ordering	
ABB Type Designation	M3AA 132SC 2
Invoice Description	M3AA 132SC 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA3__M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015220
Medium Description	7.5kW, 2 Poles, Frame Size 132, 3 Phases, 500V, 50Hz, IP55 Enclosure, IMB35/IM2001 Mounting (3GAA131130-HEK)
Short Description	7.5kW, 2P, Frame Size 132, 3PH, 500V, 50Hz, IP55, IMB35/IM2001

Electrical											
Electrical Data											
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	
D	--	50 Hz	500 V	7.50 kW	2909 r/min	10.50 A	0.900	90.70 %	24.60 N·m	8.30	
D	--	60 Hz	575 V	7.50 kW	3524 r/min	9.10 A	0.900	90.20 %	20.30 N·m	9.60	
Connection Configuration											D
Temperature Class Default											--
Input Voltage (U _{in})											500 V
Frequency (f)											50 Hz
Output Power											7.5 kW
Altitude											1000 m
Ambient Temperature											40 °C
IC Class											IC411
IE Class Data (50 Hz)											IE Class IE3 Full Load (100%) 90.7 % Partial Load (75%) 91.8 % Partial Load (50%) 92.0 %
IE Class Data (60 Hz)											IE Class IE3 Full Load (100%) 90.2 % Partial Load (75%) 90.7 % Partial Load (50%) 90.0 %
IP Class											IP55
Insulation Class											ICLF
Direction of Rotation											Both sides
Number of Poles (High)											2
Two Speed Motor											No
Type of Duty											S1
Voltage Code											E
Mechanical											
Frame Material											Aluminum
Frame Size											132
Bearing											6208-2Z/C3
Bearing NDE											6206-2Z/C3
IM Class											IMB35 IM2001
Terminator Box Location											D-End top
Dimensions											
Package Level 1 Units											0 carton
Product Net Depth / Length											487 mm
Product Net Height											298 mm
Product Net Width											262 mm
Product Net Weight											63 kg
Gross Weight											68 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories	
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors	

