




PRODUCT-DETAILS

3GAA131313-BSE  
(3GAA131313-BSE)



General Information	
Product ID	3GAA131313-BSE
ABB Type Designation	M3AA 132SC 2
Catalog Description	(3GAA131313-BSE)

Ordering	
ABB Type Designation	M3AA 132SC 2
Invoice Description	M3AA 132SC 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA2__M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN) Sweden (SE) Poland (PL)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Shanghai, China
Medium Description	7.5kW, 2 Poles, Frame Size 132, 3 Phases, 400V, 50Hz, IP55 Enclosure,

IMB5/IM3001 Mounting (3GAA131313-BSE)	
Short Description	7.5kW, 2P, Frame Size 132, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	230 V	7.50 kW	2915 r/min	24.20 A	0.870	88.50 %	24.50 N·m	7.60
Y	--	50 Hz	400 V	7.50 kW	2915 r/min	14.00 A	0.870	88.50 %	24.50 N·m	7.60
Y	--	60 Hz	460 V	7.50 kW	3520 r/min	11.80 A	0.890	89.50 %	20.30 N·m	8.70
Temperature Class Default										--
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2 Full Load (100%) 88.5 % Partial Load (75%) 88.7 % Partial Load (50%) 88.1 %
IE Class Data (60 Hz)										IE Class IE2 Full Load (100%) 89.5 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										2
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
Lubrication	For life
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	1 carton
Product Net Depth / Length	487 mm
Product Net Height	296 mm
Product Net Width	262 mm
Product Net Weight	56 kg
Gross Weight	57.38 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
Standards	IEC 60034-1
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

