



## PRODUCT-DETAILS

# 3GAA131315-ADE

## No Description Available

## "No longer for sale" replaced by 3GAA131260-

### General Information

Product ID	3GAA131315-ADE
ABB Type Designation	M3AA 132SMB 2 HO
Catalog Description	No Description Available

### Additional Information

ABB Type Designation	M3AA 132SMB 2 HO
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6308-2Z/C3
Bearing NDE	6206-2Z/C3
Country of Origin	Poland (PL) Sweden (SE)
Customs Tariff Number	85015290
Direction of Rotation	Both sides

### Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	11.00 kW	2900 r/min	11.60 A	0.870	90.30 %	36.20 N·m	8.50
D	--	50 Hz	400 V	11.00 kW	2900 r/min	20.20 A	0.870	90.30 %	36.20 N·m	8.50
D	--	60 Hz	460 V	11.00 kW	3510 r/min	16.10 A	0.940	90.90 %	29.90 N·m	9.00

Frame Material	Aluminum
Frame Size	132
Gross Weight	78.38 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 90.3 % Partial Load (75%) 90.8 % Partial Load (50%) 90.4 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 90.9 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2
Order Multiple	1 piece

Package Level 1 Units	1 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	77 kg
Product Type	3AA2_M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA131260-ADE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D