



PRODUCT-DETAILS

3GAA132004-ASE

No Description Available

"No longer for sale" replaced by 3GAA132360-

General Information												
Product ID								3GAA132004-ASE				
ABB Type Designation								M3AA 132MBA 4 HO				
Catalog Description								No Description Available				
Additional Information												
ABB Type Designation								M3AA 132MBA 4 HO				
Altitude								1000 m				
Ambient Temperature								40 °C				
Bearing								6208-2Z/C3				
Bearing NDE								6208-2Z/C3				
Country of Origin								Poland (PL) Sweden (SE)				
Customs Tariff Number								85015230				
Electrical Data												
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	
	D	--	50 Hz	230 V	9.20 kW	1460 r/min	32.30 A	0.790	89.80 %	60.10 N·m	7.30	
	Y	--	50 Hz	400 V	9.20 kW	1460 r/min	18.70 A	0.790	89.80 %	60.10 N·m	7.30	
	Y	--	60 Hz	460 V	9.20 kW	1765 r/min	16.00 A	0.790	91.30 %	49.70 N·m	8.30	
EX-Protection												Exec
Frame Material												Aluminum
Frame Size												132
Gas Group												IIB
Gross Weight												64 kg
IC Class												IC411
IE Class Data (50 Hz)												IE Class IE2 Full Load (100%) 89.8 % Partial Load (75%) 90.8 % Partial Load (50%) 90.2 %
IE Class Data (60 Hz)												IE Class IE2 Full Load (100%) 91.3 %
IM Class												IMB3 IM1001
Insulation Class												ICLF
IP Class												IP55
Lubrication												For life
Made To Order												No
Minimum Order Quantity												1 piece
Number of Poles (High)												4

Order Multiple	1 piece
Package Level 1 Units	1 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	59 kg
Product Type	3AA2__M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA132360-ASE
Selling Unit of Measure	piece
Service Factor	1.00
Standards	IEC 60034-1
Temperature Class Default	T3
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S