




PRODUCT-DETAILS

3GAA132260-BSK

IE3 Premium Efficiency Aluminum Motors, 15 kW, 400 V (3GAA132260-BSK)



General Information	
Product ID	3GAA132260-BSK
ABB Type Designation	M3AA 132SMF 4
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 15 kW, 400 V (3GAA132260-BSK)

Ordering	
ABB Type Designation	M3AA 132SMF 4
Invoice Description	M3AA 132SMF 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA3 _M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015230
Stocked At (Warehouses)	Menden, Germany
Medium Description	15kW, 4 Poles, Frame Size 132, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAA132260-BSK)

Short Description

15kW, 4P, Frame Size 132, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	15.00 kW	1464 r/min	29.70 A	0.790	92.10 %	97.52 N·m	9.00
D	--	50 Hz	230 V	15.00 kW	1464 r/min	51.40 A	0.790	92.10 %	97.52 N·m	9.00
Y	--	50 Hz	380 V	15.00 kW	1460 r/min	30.20 A	0.820	92.10 %	97.76 N·m	8.30
D	--	50 Hz	220 V	15.00 kW	1460 r/min	52.30 A	0.820	92.10 %	97.76 N·m	8.30
Y	--	50 Hz	415 V	15.00 kW	1467 r/min	29.80 A	0.760	92.10 %	97.37 N·m	9.30
Y	--	60 Hz	460 V	15.00 kW	1769 r/min	25.80 A	0.780	93.00 %	80.87 N·m	9.90

Connection Configuration	Y
Temperature Class Default	--
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	15 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 92.1 % Partial Load (75%) 92.4 % Partial Load (50%) 91.6 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 93.0 % Partial Load (75%) 93.2 % Partial Load (50%) 92.2 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions	
Package Level 1 Units	0 carton
Product Net Depth / Length	590 mm
Product Net Height	321 mm
Product Net Width	262 mm
Product Net Weight	88 kg
Gross Weight	93 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories	
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors	

