




PRODUCT-DETAILS

3GAA132300-CDE

IE2 High Efficiency Aluminum Motors, 5.5 kW, 400 V (3GAA132300-CDE)



General Information	
Product ID	3GAA132300-CDE
ABB Type Designation	M3AA 132M 4
Catalog Description	IE2 High Efficiency Aluminum Motors, 5.5 kW, 400 V (3GAA132300-CDE)

Ordering	
ABB Type Designation	M3AA 132M 4
Invoice Description	M3AA 132M 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA2__M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) China (CN) Poland (PL)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA132312-CDE
Stocked At	Shanghai, China

(Warehouses)	
Medium Description	5.5kW, 4 Poles, Frame Size 132, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB14/IM3601 Mounting (3GAA132300-CDE)
Short Description	5.5kW, 4P, Frame Size 132, 3PH, 400V, 50Hz, IP55, IMB14/IM3601

Electrical

Electrical Data											
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	
Y	--	50 Hz	690 V	5.50 kW	1465 r/min	6.30 A	0.790	89.00 %	36.00 N·m	6.20	
D	--	50 Hz	400 V	5.50 kW	1465 r/min	10.90 A	0.790	89.00 %	36.00 N·m	6.30	
D	--	60 Hz	460 V	5.50 kW	1769 r/min	9.50 A	0.790	89.70 %	29.80 N·m	7.30	
Connection Configuration											D
Temperature Class Default											--
Input Voltage (U _{in})											400 V
Frequency (f)											50 Hz
Output Power											5.5 kW
Altitude											1000 m
Ambient Temperature											40 °C
IC Class											IC411
IE Class Data (50 Hz)											IE Class IE2 Full Load (100%) 89.0 % Partial Load (75%) 89.5 % Partial Load (50%) 88.6 %
IE Class Data (60 Hz)											IE Class IE2 Full Load (100%) 89.7 % Partial Load (75%) 89.5 % Partial Load (50%) 87.8 %
IP Class											IP55
Insulation Class											ICLF
Direction of Rotation											Both sides
Number of Poles (High)											4
Two Speed Motor											No
Type of Duty											S1
Voltage Code											D

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB14 IM3601
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth /	447 mm

Length	
Product Net Height	296 mm
Product Net Width	262 mm
Product Net Weight	48 kg
Gross Weight	53 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories	
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE2 High Efficiency Aluminum Motors	
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors	

