


PRODUCT-DETAILS

3GAA132320-BSK338

IE3 Premium Efficiency Aluminum Motors, 5.5 kW, 400 V (3GAA132320-BSK338)



General Information	
Product ID	3GAA132320-BSK338
ABB Type Designation	M3AA 132MB 4
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 5.5 kW, 400 V (3GAA132320-BSK338)

Ordering	
ABB Type Designation	M3AA 132MB 4
Invoice Description	M3AA 132MB 4 / Ex ec IIC T3 Gc / Ex tc IIIB T125C Dc
Product Name	3-Phase squirrel cage motor
Product Type	3AA3__M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Romania (RO)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany
Medium Description	5.5kW, 4 Poles, Frame Size 132, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAA132320-BSK338)
Short Description	5.5kW, 4P, Frame Size 132, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data											
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	
Y	--	50 Hz	400 V	5.50 kW	1464 r/min	11.30 A	0.780	89.60 %	35.88 N-m	6.90	
D	--	50 Hz	230 V	5.50 kW	1464 r/min	19.70 A	0.780	89.60 %	35.90 N-m	6.90	
Y	--	50 Hz	380 V	5.50 kW	1457 r/min	11.70 A	0.800	89.60 %	36.04 N-m	6.30	
D	--	50 Hz	220 V	5.50 kW	1457 r/min	20.20 A	0.800	89.60 %	36.04 N-m	6.40	
Y	--	50 Hz	415 V	5.50 kW	1467 r/min	11.30 A	0.750	89.60 %	35.81 N-m	7.30	
Y	--	60 Hz	460 V	5.50 kW	1770 r/min	9.96 A	0.760	91.70 %	29.67 N-m	7.90	
Connection Configuration										Y	
Temperature Class Default										--	
Input Voltage (U _{in})										400 V	
Frequency (f)										50 Hz	
Output Power										5.5 kW	
Altitude										1000 m	
Ambient Temperature										40 °C	
IC Class										IC411	
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 89.6 % Partial Load (75%) 89.9 % Partial Load (50%) 88.9 %	
IE Class Data (60 Hz)										IE Class IE3 Full Load (100%) 91.7 % Partial Load (75%) 91.8 % Partial Load (50%) 90.7 %	
IP Class										IP55	
Insulation Class										ICLF	
Direction of Rotation										Both sides	
Number of Poles (High)										4	
Two Speed Motor										No	
Type of Duty										S1	
Voltage Code										S	

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	487 mm
Product Net Height	298 mm
Product Net Width	262 mm
Product Net Weight	68 kg
Gross Weight	73 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

