




PRODUCT-DETAILS

3GAA113320-CSE

IE2 High Efficiency Aluminum Motors, 2.2 kW,
400 V (3GAA113320-CSE)



General Information

Product ID	3GAA113320-CSE
ABB Type Designation	M3AA 112MB 6
Catalog Description	IE2 High Efficiency Aluminum Motors, 2.2 kW, 400 V (3GAA113320-CSE)

Ordering

ABB Type Designation	M3AA 112MB 6
Invoice Description	M3AA 112MB 6
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) China (CN) Romania (RO) Poland (PL)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA113312-CSE
Stocked At (Warehouses)	Menden, Germany Shanghai, China

Medium Description 2.2kW, 6 Poles, Frame Size 112, 3 Phases, 400V, 50Hz, IP55 Enclosure,

	IMB14/IM3601 Mounting (3GAA113320-CSE)
Short Description	2.2kW, 6P, Frame Size 112, 3PH, 400V, 50Hz, IP55, IMB14/IM3601

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	2.20 kW	955 r/min	5.30 A	0.720	81.90 %	21.90 N·m	5.20
D	--	50 Hz	230 V	2.20 kW	955 r/min	9.22 A	0.720	81.90 %	21.90 N·m	5.20
Y	--	60 Hz	460 V	2.20 kW	1160 r/min	5.00 A	0.650	84.40 %	18.10 N·m	5.90

Connection Configuration	Y
Temperature Class Default	--
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	2.2 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 81.9 % Partial Load (75%) 81.8 % Partial Load (50%) 79.2 %
IE Class Data (60 Hz)	IE Class IE1 Full Load (100%) 84.4 % Partial Load (75%) 83.8 % Partial Load (50%) 80.6 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	112
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB14 IM3601
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	393 mm
Product Net Height	249 mm
Product Net Width	230 mm
Product Net Weight	34 kg
Gross Weight	39 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories	
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE2 High Efficiency Aluminum Motors	
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors	

