




PRODUCT-DETAILS

3GAA132340-HDK

IE3 Premium Efficiency Aluminum Motors, 9.2 kW, 400 V (3GAA132340-HDK)



General Information

Product ID	3GAA132340-HDK
ABB Type Designation	M3AA 132MD 4
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 9.2 kW, 400 V (3GAA132340-HDK)

Ordering

ABB Type Designation	M3AA 132MD 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA3_M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) China (CN) Poland (PL)
Customs Tariff Number	85015230
Stocked At (Warehouses)	Menden, Germany
Medium Description	9.2kW, 4 Poles, Frame Size 132, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB35/IM2001 Mounting (3GAA132340-HDK)
Short Description	9.2kW, 4P, Frame Size 132, 3PH, 400V, 50Hz, IP55, IMB35/IM2001

Electrical

Electrical Data										
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	9.20 kW	1464 r/min	10.40 A	0.800	91.00 %	60.00 N·m	8.50
D	--	50 Hz	400 V	9.20 kW	1464 r/min	18.00 A	0.800	91.00 %	60.00 N·m	8.50
Y	--	50 Hz	660 V	9.20 kW	1460 r/min	10.60 A	0.830	91.00 %	60.17 N·m	7.80
D	--	50 Hz	380 V	9.20 kW	1460 r/min	18.40 A	0.830	91.00 %	60.17 N·m	7.80
D	--	50 Hz	415 V	9.20 kW	1467 r/min	17.80 A	0.780	91.00 %	59.89 N·m	9.00
D	--	60 Hz	460 V	9.20 kW	1770 r/min	15.90 A	0.780	91.70 %	49.64 N·m	9.50
Connection Configuration										D
Temperature Class										--
Default										
Input Voltage (U _{in})										400 V
Frequency (f)										50 Hz
Output Power										9.2 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 91.0 % Partial Load (75%) 91.5 % Partial Load (50%) 90.7 %
IE Class Data (60 Hz)										IE Class IE3 Full Load (100%) 91.7 % Partial Load (75%) 91.8 % Partial Load (50%) 90.9 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										4
Two Speed Motor										No
Type of Duty										S1
Voltage Code										D

Mechanical	
Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB35 IM2001
Terminator Box Location	D-End top

Dimensions	
Package Level 1 Units	0 carton
Product Net Depth / Length	487 mm
Product Net Height	298 mm
Product Net Width	262 mm
Product Net Weight	65 kg
Gross Weight	70 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

