




PRODUCT-DETAILS

3GAA114300-BDE

IE2 High Efficiency Aluminum Motors, 1.5 kW, 400 V (3GAA114300-BDE)



General Information	
Product ID	3GAA114300-BDE
ABB Type Designation	M3AA 112M 8
Catalog Description	IE2 High Efficiency Aluminum Motors, 1.5 kW, 400 V (3GAA114300-BDE)

Ordering	
ABB Type Designation	M3AA 112M 8
Invoice Description	M3AA 112M 8
Product Name	3-Phase squirrel cage motor
Product Type	3AA2__M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) China (CN) Poland (PL)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA114101-BDE 3GAA114061-BDA
Stocked At	Shanghai, China

(Warehouses)

Medium Description	1.5kW, 8 Poles, Frame Size 112, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAA114300-BDE)
Short Description	1.5kW, 8P, Frame Size 112, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	1.50 kW	690 r/min	2.40 A	0.700	74.40 %	20.70 N·m	3.20
D	--	50 Hz	400 V	1.50 kW	690 r/min	4.10 A	0.700	74.40 %	20.70 N·m	3.20
D	--	60 Hz	460 V	1.50 kW	855 r/min	3.90 A	0.610	78.60 %	16.70 N·m	4.20
Connection Configuration										D
Temperature Class Default										--
Input Voltage (U _{in})										400 V
Frequency (f)										50 Hz
Output Power										1.5 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2 Full Load (100%) 74.4 % Partial Load (75%) 74.1 % Partial Load (50%) 70.5 %
IE Class Data (60 Hz)										IE Class IE1 Full Load (100%) 78.6 % Partial Load (75%) 77.5 % Partial Load (50%) 73.2 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										8
Two Speed Motor										No
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Aluminum
Frame Size	112
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	393 mm
Product Net Height	249 mm

Product Net Width	230 mm
Product Net Weight	28 kg
Gross Weight	33 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

