



PRODUCT-DETAILS

3GAA131110-BDP
QAL 71MB 2

General Information

Product ID	3GAA131110-BDP
ABB Type Designation	QAL 132SA 2
Catalog Description	QAL 71MB 2

Ordering

ABB Type Designation	QAL 132SA 2
Invoice Description	QAL 71MB 2
Product Name	3-Phase squirrel cage motor
Product Type	QAL
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015220

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque
D	--	50 Hz	380 V	5.50 kW	2930 r/min	10.70 A	0.880	89.20 %	17.93 N·m

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical	
Frame Material	Aluminum
Frame Size	132
Bearing	6308-2Z/C3
Bearing NDE	6308-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions	
Package Level 1 Units	0 carton
Product Net Weight	40 kg
Gross Weight	45 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Classifications	
UNSPSC	26101100

Categories	
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Aluminum Motors	