



PRODUCT-DETAILS

3GAA133315-ARE

No Description Available

"No longer for sale" replaced by 3GAA133340-

General Information																																			
Product ID	3GAA133315-ARE																																		
ABB Type Designation	M3AA 132MD 6																																		
Catalog Description	No Description Available																																		
Additional Information																																			
ABB Type Designation	M3AA 132MD 6																																		
Altitude	1000 m																																		
Ambient Temperature	40 °C																																		
Bearing	6208-2Z/C3																																		
Bearing NDE	6208-2Z/C3																																		
Country of Origin	Spain (ES) Sweden (SE)																																		
Customs Tariff Number	85015220																																		
Direction of Rotation	Both sides																																		
Electrical Data																																			
<table><tr><th>Conn</th><th>Temp Class</th><th>Freq</th><th>Voltage</th><th>Power</th><th>Speed</th><th>Current</th><th>Power Factor</th><th>Efficiency</th></tr><tr><td>D</td><td>--</td><td>60 Hz</td><td>220 V</td><td>7.50 kW</td><td>1170 r/min</td><td>36.00 A</td><td>0.610</td><td>88.50 %</td></tr><tr><td>Y</td><td>--</td><td>60 Hz</td><td>380 V</td><td>7.50 kW</td><td>1170 r/min</td><td>20.80 A</td><td>0.610</td><td>88.50 %</td></tr></table>									Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	D	--	60 Hz	220 V	7.50 kW	1170 r/min	36.00 A	0.610	88.50 %	Y	--	60 Hz	380 V	7.50 kW	1170 r/min	20.80 A	0.610	88.50 %
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency																											
D	--	60 Hz	220 V	7.50 kW	1170 r/min	36.00 A	0.610	88.50 %																											
Y	--	60 Hz	380 V	7.50 kW	1170 r/min	20.80 A	0.610	88.50 %																											
Frame Size	132																																		
Gross Weight	62.38 kg																																		
IC Class	IC411																																		
IM Class	IMB3 IM1001																																		
Insulation Class	ICLF																																		
IP Class	IP55																																		
Lubrication	For life																																		
Made To Order	No																																		
Minimum Order Quantity	1 piece																																		
Number of Poles (High)	6																																		
Order Multiple	1 piece																																		
Package Level 1 Units	0 carton																																		
Product Name	3-Phase squirrel cage motor																																		
Product Net Weight	61 kg																																		

Product Type	3AA2__M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA133340-ARE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Stocked At (Warehouses)	Menden, Germany
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	R