


PRODUCT-DETAILS

3GAA131130-BSJ

IE3 Premium Efficiency Aluminum Motors, 7.5 kW, 400 V (3GAA131130-BSJ)



General Information	
Product ID	3GAA131130-BSJ
ABB Type Designation	M3AA 132SC 2
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 7.5 kW, 400 V (3GAA131130-BSJ)

Ordering	
ABB Type Designation	M3AA 132SC 2
Invoice Description	M3AA 132SC 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA0_M3AA_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN) Finland (FI)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA131613-BSJ
Stocked At (Warehouses)	Vittuone, Italy

Medium Description	7.5kW, 2 Poles, Frame Size 132, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAA131130-BSJ)
Short Description	7.5kW, 2P, Frame Size 132, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	7.50 kW	2909 r/min	13.10 A	0.900	90.10 %	24.60 N·m	8.30
D	--	50 Hz	230 V	7.50 kW	2909 r/min	22.80 A	0.900	90.10 %	24.60 N·m	8.30
Y	--	50 Hz	415 V	7.50 kW	2917 r/min	12.70 A	0.900	90.10 %	24.60 N·m	9.00

Connection Configuration	Y
Temperature Class Default	--
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	7.5 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 90.1 % Partial Load (75%) 91.1 % Partial Load (50%) 91.2 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	487 mm
Product Net Height	298 mm
Product Net Width	262 mm
Product Net Weight	63 kg

Gross Weight

68 kg

Environmental

WEEE Category

5. Small Equipment (No External Dimension More Than 50 cm)

SCIP

27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC

26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

