




PRODUCT-DETAILS

3GAA133350-ASK

IE3 Premium Efficiency Aluminum Motors, 5.5 kW, 400 V (3GAA133350-ASK)



General Information	
Product ID	3GAA133350-ASK
ABB Type Designation	M3AA 132ME 6
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 5.5 kW, 400 V (3GAA133350-ASK)

Ordering	
ABB Type Designation	M3AA 132ME 6
Invoice Description	M3AA 132ME 6
Product Name	3-Phase squirrel cage motor
Product Type	3AA3_M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN) Finland (FI)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany Sant Quirze del Vallés - BCN, Spain Vittuone, Italy
Medium Description	5.5kW, 6 Poles, Frame Size 132, 3 Phases, 400V, 50Hz, IP55 Enclosure,

IMB3/IM1001 Mounting (3GAA133350-ASK)	
Short Description	5.5kW, 6P, Frame Size 132, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	5.50 kW	973 r/min	12.00 A	0.740	88.00 %	53.90 N·m	5.80
D	--	50 Hz	230 V	5.50 kW	973 r/min	20.70 A	0.740	88.00 %	53.90 N·m	5.80
Y	--	50 Hz	380 V	5.50 kW	969 r/min	12.20 A	0.770	88.00 %	54.20 N·m	5.30
D	--	50 Hz	220 V	5.50 kW	969 r/min	21.10 A	0.770	88.00 %	54.20 N·m	5.30
Y	--	50 Hz	415 V	5.50 kW	976 r/min	12.00 A	0.710	88.00 %	53.80 N·m	6.10
Y	--	60 Hz	460 V	5.50 kW	1177 r/min	10.40 A	0.720	91.00 %	44.60 N·m	6.60

Connection Configuration	Y
Temperature Class Default	--
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	5.5 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 88.0 % Partial Load (75%) 88.4 % Partial Load (50%) 87.4 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 91.0 % Partial Load (75%) 91.3 % Partial Load (50%) 90.4 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	487 mm

Product Net Height	298 mm
Product Net Width	262 mm
Product Net Weight	63 kg
Gross Weight	68 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

