




PRODUCT-DETAILS

3GAA132300-ASE053

IE2 High Efficiency Aluminum Motors, 5.5 kW,
400 V (3GAA132300-ASE053)



General Information

Product ID	3GAA132300-ASE053
ABB Type Designation	M3AA 132M 4
Catalog Description	IE2 High Efficiency Aluminum Motors, 5.5 kW, 400 V (3GAA132300-ASE053)

Ordering

ABB Type Designation	M3AA 132M 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) China (CN) Poland (PL)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany
Medium Description	5.5kW, 4P, Frame Size 132, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA132300-ASE053)
Short Description	5.5kW, 4P, Frame Size 132, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data										
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	5.50 kW	1465 r/min	10.90 A	0.790	89.00 %	36.00 N·m	6.30
D	--	50 Hz	230 V	5.50 kW	1465 r/min	19.00 A	0.790	89.00 %	36.00 N·m	6.30
Y	--	60 Hz	460 V	5.50 kW	1769 r/min	9.50 A	0.790	89.70 %	29.80 N·m	7.30
Connection Configuration										Y
Temperature Class Default										--
Input Voltage (U _{in})										400 V
Frequency (f)										50 Hz
Output Power										5.5 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2
										Full Load (100%) 89.0 %
										Partial Load (75%) 89.5 %
										Partial Load (50%) 88.6 %
IE Class Data (60 Hz)										IE Class IE2
										Full Load (100%) 89.7 %
										Partial Load (75%) 89.5 %
										Partial Load (50%) 87.8 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										4
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	487 mm
Product Net Height	296 mm
Product Net Width	262 mm
Product Net Weight	48 kg
Gross Weight	53 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

