



PRODUCT-DETAILS

3GAA132310-ADE

IE2 High Efficiency Aluminum Motors, 7.5 kW, 400 V (3GAA132310-ADE)



General Information	
Product ID	3GAA132310-ADE
ABB Type Designation	M3AA 132MA 4
Catalog Description	IE2 High Efficiency Aluminum Motors, 7.5 kW, 400 V (3GAA132310-ADE)

Ordering	
ABB Type Designation	M3AA 132MA 4
Invoice Description	M3AA 132MA 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA2__M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN) Finland (FI) Poland (PL)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA132444-ADE 3GAA132314-ADE
Stocked At	Menden, Germany

(Warehouses)	Shanghai, China Vittuone, Italy
Medium Description	7.5kW, 4 Poles, Frame Size 132, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA132310-ADE)
Short Description	7.5kW, 4P, Frame Size 132, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	7.50 kW	1460 r/min	8.57 A	0.790	88.70 %	49.00 N·m	6.40
D	--	50 Hz	400 V	7.50 kW	1460 r/min	14.70 A	0.790	88.70 %	49.00 N·m	6.40
D	--	60 Hz	460 V	7.50 kW	1764 r/min	12.80 A	0.810	89.50 %	40.60 N·m	7.50
Connection Configuration										D
Temperature Class Default										--
Input Voltage (U _{in})										400 V
Frequency (f)										50 Hz
Output Power										7.5 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2 Full Load (100%) 88.7 % Partial Load (75%) 89.5 % Partial Load (50%) 89.0 %
IE Class Data (60 Hz)										IE Class IE2 Full Load (100%) 89.5 % Partial Load (75%) 89.6 % Partial Load (50%) 88.3 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										4
Two Speed Motor										No
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
-----------------------	----------

Product Net Depth / Length	447 mm
Product Net Height	296 mm
Product Net Width	262 mm
Product Net Weight	59 kg
Gross Weight	64 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

