




PRODUCT-DETAILS

3GAA132320-ASK339

IE3 Premium Efficiency Aluminum Motors, 5.5 kW, 400 V (3GAA132320-ASK339)



General Information

Product ID	3GAA132320-ASK339
ABB Type Designation	M3AA 132MB 4
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 5.5 kW, 400 V (3GAA132320-ASK339)

Ordering

ABB Type Designation	M3AA 132MB 4
Invoice Description	M3AA 132MB 4 / Ex ec IIC T3 Gc / Ex tc IIC T125C Dc
Product Name	3-Phase squirrel cage motor
Product Type	3AA3 _M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Romania (RO)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany
Medium Description	5.5kW, 4 Poles, Frame Size 132, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA132320-ASK339)
Short Description	5.5kW, 4P, Frame Size 132, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	5.50 kW	1464 r/min	11.30 A	0.780	89.60 %	35.88 N·m	6.90
D	--	50 Hz	230 V	5.50 kW	1464 r/min	19.70 A	0.780	89.60 %	35.90 N·m	6.90
Y	--	50 Hz	380 V	5.50 kW	1457 r/min	11.70 A	0.800	89.60 %	36.04 N·m	6.30
D	--	50 Hz	220 V	5.50 kW	1457 r/min	20.20 A	0.800	89.60 %	36.04 N·m	6.40
Y	--	50 Hz	415 V	5.50 kW	1467 r/min	11.30 A	0.750	89.60 %	35.81 N·m	7.30
Y	--	60 Hz	460 V	5.50 kW	1770 r/min	9.96 A	0.760	91.70 %	29.67 N·m	7.90
Connection Configuration										Y
Temperature Class Default										--
Input Voltage (U _{in})										400 V
Frequency (f)										50 Hz
Output Power										5.5 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 89.6 % Partial Load (75%) 89.9 % Partial Load (50%) 88.9 %
IE Class Data (60 Hz)										IE Class IE3 Full Load (100%) 91.7 % Partial Load (75%) 91.8 % Partial Load (50%) 90.7 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										4
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	487 mm
Product Net Height	298 mm
Product Net Width	262 mm
Product Net Weight	68 kg
Gross Weight	73 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

