



PRODUCT-DETAILS

3GAA161034-ASG

No Description Available

"No longer for sale" replaced by 3GAA161440-

General Information	
Product ID	3GAA161034-ASG
ABB Type Designation	M3AA 160MLD 2
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M3AA 160MLD 2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6309-2Z/C3
Bearing NDE	6209-2Z/C3
Country of Origin	Sweden (SE)
Customs Tariff Number	85015230
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	230 V	22.00 kW	2933 r/min	66.10 A	0.910
Y	--	50 Hz	400 V	22.00 kW	2933 r/min	38.00 A	0.910
Y	--	50 Hz	415 V	22.00 kW	2940 r/min	37.40 A	0.890
Y	--	60 Hz	460 V	22.00 kW	3546 r/min	32.80 A	0.910

Frame Material	Aluminum
Frame Size	160
Gross Weight	123 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2
	Full Load (100%) 91.7 %
	Partial Load (75%) 92.9 %
IE Class Data (60 Hz)	Partial Load (50%) 92.6 %
	IE Class IE3
	Full Load (100%) 92.5 %
IM Class	Partial Load (75%) 92.9 %
	Partial Load (50%) 92.1 %
Insulation Class	IMB3 IM1001
IP Class	ICLF
	IP55

Made To Order	No
Minimum Order Quantity	1 piece
Moment of Inertia	0.00000 kg/m³
Number of Poles (High)	2
Package Level 1 Units	0 pallet (lift)
Product Name	3-Phase squirrel cage motor
Product Net Weight	123 kg
Product Type	3AA2__M3AA_IE2_AA
Quote Only	No
Replaced Product ID (OLD)	3GAA161104-ASC
Replacement Product ID (NEW)	3GAA161440-ASG
Selling Unit of Measure	piece
Service Factor	0.00
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S