



PRODUCT-DETAILS

3GAA161037-ASG

No Description Available

"No longer for sale" replaced by 3GAA161430-

General Information	
Product ID	3GAA161037-ASG
ABB Type Designation	M3AA 160MLC 2
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M3AA 160MLC 2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6309-2Z/C3
Bearing NDE	6209-2Z/C3
Country of Origin	Sweden (SE)
Customs Tariff Number	85015230
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	230 V	18.50 kW	2932 r/min	54.80 A	0.920
Y	--	50 Hz	400 V	18.50 kW	2932 r/min	31.50 A	0.920
Y	--	50 Hz	415 V	18.50 kW	2938 r/min	30.70 A	0.910
Y	--	60 Hz	460 V	18.50 kW	3543 r/min	27.20 A	0.920

Frame Material	Aluminum
Frame Size	160
Gross Weight	123 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 92.0 % Partial Load (75%) 93.0 % Partial Load (50%) 92.9 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 92.5 % Partial Load (75%) 92.9 % Partial Load (50%) 92.2 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55

Made To Order	No
Minimum Order Quantity	1 piece
Moment of Inertia	0.00000 kg/m³
Number of Poles (High)	2
Package Level 1 Units	0 pallet (lift)
Product Name	3-Phase squirrel cage motor
Product Net Weight	123 kg
Product Type	3AA2__M3AA_IE2_AA
Quote Only	No
Replaced Product ID (OLD)	3GAA161103-ASC 3GAA161033-ASG
Replacement Product ID (NEW)	3GAA161430-ASG
Selling Unit of Measure	piece
Service Factor	0.00
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S