



PRODUCT-DETAILS

3GAA133311-AEE

No Description Available

"No longer for sale" replaced by 3GAA133100-

General Information	
Product ID	3GAA133311-AEE
ABB Type Designation	M3AA 132S 6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M3AA 132S 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
Country of Origin	Spain (ES) Sweden (SE)
Customs Tariff Number	85015220
Direction of Rotation	Both sides

Electrical Data										
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	500 V	3.00 kW	960 r/min	6.30 A	0.650	83.30 %	29.80 N·m	4.30
D	--	60 Hz	575 V	3.00 kW	1175 r/min	5.10 A	0.680	85.40 %	24.30 N·m	6.40

Frame Material	Aluminum
Frame Size	132
Gross Weight	40.38 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 83.3 % Partial Load (75%) 83.6 % Partial Load (50%) 81.7 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece

Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	1 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	39 kg
Product Type	3AA2__M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA133100-AEE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	E