




PRODUCT-DETAILS

3GAA133330-ASE

IE2 High Efficiency Aluminum Motors, 5.5 kW,  
400 V (3GAA133330-ASE)



General Information

Product ID	3GAA133330-ASE
ABB Type Designation	M3AA 132MC 6
Catalog Description	IE2 High Efficiency Aluminum Motors, 5.5 kW, 400 V (3GAA133330-ASE)

Ordering

ABB Type Designation	M3AA 132MC 6
Invoice Description	M3AA 132MC 6
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN) Finland (FI) Poland (PL)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA133444-ASE 3GAA133314-ASE
Stocked At (Warehouses)	Menden, Germany Sant Quirze del Vallés - BCN, Spain Shanghai, China Vittuone, Italy

Medium Description	5.5kW, 6 Poles, Frame Size 132, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA133330-ASE)
Short Description	5.5kW, 6P, Frame Size 132, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	5.50 kW	965 r/min	13.30 A	0.670	86.10 %	54.30 N·m	6.20
D	--	50 Hz	230 V	5.50 kW	965 r/min	24.30 A	0.670	86.10 %	54.30 N·m	6.20
Y	--	60 Hz	460 V	5.50 kW	1165 r/min	11.80 A	0.670	87.30 %	44.96 N·m	6.80

Connection Configuration	Y
Temperature Class Default	--
Input Voltage (U <sub>in</sub> )	400 V
Frequency (f)	50 Hz
Output Power	5.5 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 86.1 % Partial Load (75%) 85.6 % Partial Load (50%) 83.0 %
IE Class Data (60 Hz)	IE Class IE1 Full Load (100%) 87.3 % Partial Load (75%) 86.2 % Partial Load (50%) 83.0 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	487 mm
Product Net Height	296 mm
Product Net Width	262 mm
Product Net Weight	59 kg
Gross Weight	64 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)
Classifications	
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

