




PRODUCT-DETAILS

3GAA133340-JSK

IE3 Premium Efficiency Aluminum Motors, 4 kW,  
400 V (3GAA133340-JSK)



General Information

Product ID	3GAA133340-JSK
ABB Type Designation	M3AA 132MD 6
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 4 kW, 400 V (3GAA133340-JSK)

Ordering

ABB Type Designation	M3AA 132MD 6
Invoice Description	M3AA 132MD 6
Product Name	3-Phase squirrel cage motor
Product Type	3AA3_M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015220
Medium Description	4kW, 6 Poles, Frame Size 132, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB34/IM2101 Mounting (3GAA133340-JSK)
Short Description	4kW, 6P, Frame Size 132, 3PH, 400V, 50Hz, IP55, IMB34/IM2101

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	4.00 kW	973 r/min	9.10 A	0.720	86.80 %	39.20 N·m	5.60
D	--	50 Hz	230 V	4.00 kW	973 r/min	15.70 A	0.720	86.80 %	39.20 N·m	5.60
Y	--	50 Hz	380 V	4.00 kW	968 r/min	9.30 A	0.740	86.80 %	39.40 N·m	5.10
D	--	50 Hz	220 V	4.00 kW	968 r/min	16.10 A	0.740	86.80 %	39.40 N·m	5.10
Y	--	50 Hz	415 V	4.00 kW	975 r/min	9.00 A	0.690	86.80 %	39.20 N·m	6.00
Y	--	60 Hz	460 V	4.00 kW	1176 r/min	8.00 A	0.690	89.50 %	32.40 N·m	6.20

Connection Configuration	Y
Temperature Class	--
Default	
Input Voltage (U <sub>in</sub> )	400 V
Frequency (f)	50 Hz
Output Power	4 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 86.8 % Partial Load (75%) 87.6 % Partial Load (50%) 86.8 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 89.5 % Partial Load (75%) 89.9 % Partial Load (50%) 88.9 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB34 IM2101
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	487 mm
Product Net Height	298 mm
Product Net Width	262 mm
Product Net Weight	67 kg
Gross Weight	72 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

---

Classifications

---

UNSPSC	26101100
--------	----------

---

---

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

