

PRODUCT-DETAILS

3GAA161420-ADK

IE3 Premium Efficiency Aluminum Motors, 15 kW, 400 V (3GAA161420-ADK)



General Information	
Product ID	3GAA161420-ADK
ABB Type Designation	M3AA 160MLB 2
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 15 kW, 400 V (3GAA161420-ADK)

Ordering	
ABB Type Designation	M3AA 160MLB 2
Invoice Description	M3AA 160MLB 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA3_M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Poland (PL) Finland (FI) China (CN)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA161052-ADK
Stocked At	Menden, Germany

(Warehouses)	Sant Quirze del Vallés - BCN, Spain
Medium Description	15kW, 2 Poles, Frame Size 160, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA161420-ADK)
Short Description	15kW, 2P, Frame Size 160, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	15.00 kW	2947 r/min	15.50 A	0.880	91.90 %	48.60 N·m	8.20
D	--	50 Hz	400 V	15.00 kW	2947 r/min	26.70 A	0.880	91.90 %	48.60 N·m	8.20
Y	--	50 Hz	660 V	15.00 kW	2939 r/min	15.80 A	0.900	91.90 %	48.70 N·m	7.90
D	--	50 Hz	380 V	15.00 kW	2939 r/min	27.50 A	0.900	91.90 %	48.70 N·m	7.90
D	--	50 Hz	415 V	15.00 kW	2960 r/min	26.60 A	0.860	91.90 %	48.40 N·m	8.70
D	--	60 Hz	460 V	15.00 kW	3554 r/min	23.20 A	0.890	91.00 %	40.30 N·m	8.50
Connection Configuration										D
Temperature Class Default										--
Input Voltage (U _{in})										400 V
Frequency (f)										50 Hz
Output Power										15 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 91.9 % Partial Load (75%) 92.0 % Partial Load (50%) 91.4 %
IE Class Data (60 Hz)										IE Class IE3 Full Load (100%) 91.0 % Partial Load (75%) 90.4 % Partial Load (50%) 89.6 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										2
Two Speed Motor										No
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Aluminum
Frame Size	160
Bearing	6309-2Z/C3
Bearing NDE	6209-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions	
Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	681 mm
Product Net Height	370 mm
Product Net Width	310 mm
Product Net Weight	123 kg
Gross Weight	133 kg

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

