

PRODUCT-DETAILS

# 3GAA161430-ADG

## (3GAA161430-ADG)



General Information	
Product ID	3GAA161430-ADG
ABB Type Designation	M3AA 160MLC 2
Catalog Description	(3GAA161430-ADG)

Ordering	
ABB Type Designation	M3AA 160MLC 2
Invoice Description	M3AA 160MLC 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) China (CN) Poland (PL)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA161037-ADG
Stocked At	Menden, Germany

(Warehouses)

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	18.50 kW	2932 r/min	18.30 A	0.920	92.00 %	60.20 N·m	7.50
D	--	50 Hz	400 V	18.50 kW	2932 r/min	31.50 A	0.920	92.00 %	60.20 N·m	7.50
D	--	50 Hz	415 V	18.50 kW	2938 r/min	30.70 A	0.900	92.10 %	60.20 N·m	8.00
D	--	60 Hz	440 V	18.50 kW	3536 r/min	28.60 A	0.920	92.20 %	49.90 N·m	7.90
D	--	60 Hz	460 V	18.50 kW	3543 r/min	27.20 A	0.920	92.40 %	49.80 N·m	8.70

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 92.0 % Partial Load (75%) 93.1 % Partial Load (50%) 93.1 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 92.2 % Partial Load (75%) 92.8 % Partial Load (50%) 92.3 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Aluminum
Frame Size	160
Bearing	6309-2Z/C3
Bearing NDE	6209-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Weight	123 kg
Gross Weight	133 kg

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories	
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors	

