



PRODUCT-DETAILS

3GAA161430-BSG

IE2 High Efficiency Aluminum Motors, 18.5 kW,
400 V (3GAA161430-BSG)



General Information

Product ID	3GAA161430-BSG
ABB Type Designation	M3AA 160MLC 2
Catalog Description	IE2 High Efficiency Aluminum Motors, 18.5 kW, 400 V (3GAA161430-BSG)

Ordering

ABB Type Designation	M3AA 160MLC 2
Invoice Description	M3AA 160MLC 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA161063-BSA 3GAA161037-BSG
Stocked At (Warehouses)	Menden, Germany
Medium Description	18.5kW, 2 Poles, Frame Size 160, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAA161430-BSG)
Short Description	18.5kW, 2P, Frame Size 160, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	18.50 kW	2932 r/min	31.50 A	0.920	92.00 %	60.20 N·m	7.50
D	--	50 Hz	230 V	18.50 kW	2932 r/min	55.20 A	0.920	92.00 %	60.20 N·m	7.50
Y	--	50 Hz	415 V	18.50 kW	2938 r/min	30.70 A	0.900	92.10 %	60.20 N·m	8.00
Y	--	60 Hz	440 V	18.50 kW	3536 r/min	28.60 A	0.920	92.20 %	49.90 N·m	7.90
Y	--	60 Hz	460 V	18.50 kW	3543 r/min	27.20 A	0.920	92.40 %	49.80 N·m	8.70

Connection Configuration	Y
Temperature Class	--
Default	
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	18.5 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 92.0 % Partial Load (75%) 93.1 % Partial Load (50%) 93.1 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 92.2 % Partial Load (75%) 92.8 % Partial Load (50%) 92.3 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	160
Bearing	6309-2Z/C3
Bearing NDE	6209-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	681 mm
Product Net Height	370 mm
Product Net Width	310.5 mm
Product Net Weight	123 kg
Gross Weight	133 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

SCIP

27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC

26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

