



PRODUCT-DETAILS

3GAA161440-ASG

IE2 High Efficiency Aluminum Motors, 22 kW, 400 V (3GAA161440-ASG)



General Information

Product ID	3GAA161440-ASG
ABB Type Designation	M3AA 160MLD 2
Catalog Description	IE2 High Efficiency Aluminum Motors, 22 kW, 400 V (3GAA161440-ASG)

Ordering

ABB Type Designation	M3AA 160MLD 2
Invoice Description	M3AA 160MLD 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Spain (ES) Finland (FI) Poland (PL)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA161034-ASG 3GAA161064-ASA
Stocked At (Warehouses)	Menden, Germany
Medium Description	22kW, 2 Poles, Frame Size 160, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA161440-ASG)

Short Description22kW, 2P, Frame Size 160, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	22.00 kW	2933 r/min	38.00 A	0.900	91.70 %	71.60 N·m	8.10
D	--	50 Hz	230 V	22.00 kW	2933 r/min	67.20 A	0.900	91.70 %	71.60 N·m	8.10
Y	--	50 Hz	415 V	22.00 kW	2940 r/min	37.40 A	0.890	91.90 %	71.60 N·m	8.50
Y	--	60 Hz	440 V	22.00 kW	3539 r/min	34.00 A	0.920	92.20 %	59.30 N·m	8.60
Y	--	60 Hz	460 V	22.00 kW	3546 r/min	32.80 A	0.910	92.40 %	59.20 N·m	9.30

Connection Configuration	Y
Temperature Class	--
Default	
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	22 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 91.7 % Partial Load (75%) 92.8 % Partial Load (50%) 92.8 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 92.2 % Partial Load (75%) 92.8 % Partial Load (50%) 92.3 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	160
Bearing	6309-2Z/C3
Bearing NDE	6209-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	681 mm
Product Net Height	370 mm
Product Net Width	310.5 mm
Product Net Weight	123 kg
Gross Weight	133 kg

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)
Classifications	
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

