



PRODUCT-DETAILS

# 3GAA161410-BDK

## IE3 Premium Efficiency Aluminum Motors, 11 kW, 400 V (3GAA161410-BDK)



General Information

Product ID	3GAA161410-BDK
ABB Type Designation	M3AA 160MLA 2
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 11 kW, 400 V (3GAA161410-BDK)

Ordering

ABB Type Designation	M3AA 160MLA 2
Invoice Description	M3AA 160MLA 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA3_M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Spain (ES) Finland (FI) China (CN) Poland (PL)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA161051-BDK
Stocked At (Warehouses)	Menden, Germany Sant Quirze del Vallés - BCN, Spain

Medium Description 11kW, 2 Poles, Frame Size 160, 3 Phases, 400V, 50Hz, IP55 Enclosure,

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	11.00 kW	2943 r/min	11.10 A	0.910	91.20 %	35.57 N·m	7.20
D	--	50 Hz	400 V	11.00 kW	2943 r/min	19.10 A	0.910	91.20 %	35.57 N·m	7.20
Y	--	50 Hz	660 V	11.00 kW	2933 r/min	11.50 A	0.920	91.20 %	35.65 N·m	6.50
D	--	50 Hz	380 V	11.00 kW	2933 r/min	20.10 A	0.920	91.20 %	35.65 N·m	6.50
D	--	50 Hz	415 V	11.00 kW	2946 r/min	18.50 A	0.900	91.20 %	35.52 N·m	7.70
D	--	60 Hz	460 V	11.00 kW	3549 r/min	16.60 A	0.910	91.00 %	29.54 N·m	8.70

Connection Configuration	D
Temperature Class Default	--
Input Voltage (U <sub>in</sub> )	400 V
Frequency (f)	50 Hz
Output Power	11 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 91.2 % Partial Load (75%) 91.7 % Partial Load (50%) 91.3 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 91.0 % Partial Load (75%) 91.1 % Partial Load (50%) 89.9 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Aluminum
Frame Size	160
Bearing	6309-2Z/C3
Bearing NDE	6209-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	681 mm
Product Net Height	370 mm
Product Net Width	310 mm
Product Net Weight	106 kg
Gross Weight	116 kg

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories	
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors	

