

PRODUCT-DETAILS

# 3GAA161420-HDG

## (3GAA161420-HDG)



General Information	
Product ID	3GAA161420-HDG
ABB Type Designation	M3AA 160MLB 2
Catalog Description	(3GAA161420-HDG)

Ordering	
ABB Type Designation	M3AA 160MLB 2
Invoice Description	M3AA 160MLB 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA161036-HDG

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	15.00 kW	2934 r/min	15.10 A	0.900	91.50 %	48.80 N·m	7.50
D	--	50 Hz	400 V	15.00 kW	2934 r/min	26.00 A	0.900	91.50 %	48.80 N·m	7.50
D	--	50 Hz	415 V	15.00 kW	2941 r/min	25.20 A	0.900	91.70 %	48.80 N·m	8.10
D	--	60 Hz	440 V	15.00 kW	3539 r/min	23.50 A	0.900	91.80 %	40.40 N·m	7.90
D	--	60 Hz	460 V	15.00 kW	3545 r/min	22.40 A	0.900	92.10 %	40.40 N·m	8.70
Temperature Class										--
Default										
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2 Full Load (100%) 91.5 % Partial Load (75%) 92.5 % Partial Load (50%) 92.2 %
IE Class Data (60 Hz)										IE Class IE3 Full Load (100%) 91.8 % Partial Load (75%) 92.2 % Partial Load (50%) 91.4 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										2
Two Speed Motor										No
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Aluminum
Frame Size	160
Bearing	6309-2Z/C3
Bearing NDE	6209-2Z/C3
IM Class	IMB35 IM2001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Weight	105 kg
Gross Weight	115 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

