



## PRODUCT-DETAILS

# 3GAA168230-ADG

## No Description Available

## "No longer for sale" replaced by 3GAA169421-

### General Information

Product ID	3GAA168230-ADG
ABB Type Designation	M3AA 160MLB 2/4
Catalog Description	No Description Available

### Additional Information

ABB Type Designation	M3AA 160MLB 2/4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6309-2Z/C3
Bearing NDE	6209-2Z/C3
Country of Origin	Sweden (SE)
Customs Tariff Number	85015230
Direction of Rotation	Both sides

#### Electrical Data

Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
--	50 Hz	400 V	15.00 kW	2928 r/min	26.20 A	0.920
--	50 Hz	400 V	7.50 kW	1467 r/min	16.30 A	0.780

Frame Material	Aluminum
Frame Size	160
Gross Weight	123 kg
IC Class	IC411
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2
Number of Poles (Low)	4
Order Multiple	1 piece
Package Level 1 Units	0 pallet (lift)
Product Name	3-Phase squirrel cage motor
Product Net Weight	123 kg
Product Type	3AA2_M3AA_IE2_AA
Quote Only	No
Replaced Product ID (OLD)	3GAA168360-ADC

Replacement Product ID (NEW)	3GAA169421-ADG
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	Yes
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D