



PRODUCT-DETAILS

3GAA164032-HDG

No Description Available

"No longer for sale" replaced by 3GAA164420-

General Information	
Product ID	3GAA164032-HDG
ABB Type Designation	M3AA 160MLB 8
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M3AA 160MLB 8
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6309-2Z/C3
Bearing NDE	6209-2Z/C3
Country of Origin	Sweden (SE) Poland (PL)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	400 V	5.50 kW	726 r/min	13.90 A	0.670
Y	--	50 Hz	690 V	5.50 kW	726 r/min	8.10 A	0.670
D	--	50 Hz	415 V	5.50 kW	728 r/min	14.10 A	0.640
D	--	60 Hz	460 V	5.50 kW	881 r/min	12.20 A	0.650

Frame Material	Aluminum
Frame Size	160
Gross Weight	116 kg
IC Class	IC411
IM Class	IMB35 IM2001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Moment of Inertia	0.00000 kg/m³
Number of Poles (High)	8
Package Level 1 Units	0 pallet (lift)
Pre Modified Motor	3GAA164032-ADG

Product ID	
Product Name	3-Phase squirrel cage motor
Product Net Weight	106 kg
Product Type	3AA2__M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA164420-HDG
Selling Unit of Measure	piece
Service Factor	0.00
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D