



PRODUCT-DETAILS

3GAA164420-ASG

IE2 High Efficiency Aluminum Motors, 5.5 kW, 400 V (3GAA164420-ASG)



General Information	
Product ID	3GAA164420-ASG
ABB Type Designation	M3AA 160MLB 8
Catalog Description	IE2 High Efficiency Aluminum Motors, 5.5 kW, 400 V (3GAA164420-ASG)

Ordering	
ABB Type Designation	M3AA 160MLB 8
Invoice Description	M3AA 160MLB 8
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GAA164062-ASA 3GAA164032-ASG
Medium Description	5.5kW, 8 Poles, Frame Size 160, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA164420-ASG)

Short Description

5.5kW, 8P, Frame Size 160, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	5.50 kW	726 r/min	13.90 A	0.670	84.60 %	72.30 N·m	5.60
D	--	50 Hz	230 V	5.50 kW	726 r/min	24.90 A	0.670	84.60 %	72.30 N·m	5.60
Y	--	50 Hz	415 V	5.50 kW	728 r/min	14.10 A	0.640	84.50 %	72.30 N·m	5.70
Y	--	60 Hz	440 V	5.50 kW	879 r/min	12.40 A	0.670	86.30 %	59.70 N·m	5.80
Y	--	60 Hz	460 V	5.50 kW	881 r/min	12.20 A	0.650	86.40 %	59.60 N·m	6.20

Connection Configuration	Y
Temperature Class Default	--
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	5.5 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 84.5 % Partial Load (75%) 85.4 % Partial Load (50%) 83.8 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 86.3 % Partial Load (75%) 86.9 % Partial Load (50%) 85.3 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	8
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	160
Bearing	6309-2Z/C3
Bearing NDE	6209-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	584 mm
Product Net Height	370 mm
Product Net Width	310.5 mm

Product Net Weight	98 kg
Gross Weight	108 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

