

PRODUCT-DETAILS

# 3GAA182430-HSG

## IE2 High Efficiency Aluminum Motors, 30 kW, 400 V (3GAA182430-HSG)



General Information	
Product ID	3GAA182430-HSG
ABB Type Designation	M3AA 180MLC 4
Catalog Description	IE2 High Efficiency Aluminum Motors, 30 kW, 400 V (3GAA182430-HSG)

Ordering	
ABB Type Designation	M3AA 180MLC 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015230
Medium Description	30kW, 4 Poles, Frame Size 180, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB35/IM2001 Mounting (3GAA182430-HSG)
Short Description	30kW, 4P, Frame Size 180, 3PH, 400V, 50Hz, IP55, IMB35/IM2001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	30.00 kW	1474 r/min	56.50 A	0.830	92.30 %	194.00 N·m	7.30
D	--	50 Hz	230 V	30.00 kW	1474 r/min	99.90 A	0.830	92.30 %	194.00 N·m	7.30
Y	--	50 Hz	415 V	30.00 kW	1477 r/min	55.70 A	0.810	92.40 %	194.00 N·m	7.70
Y	--	60 Hz	440 V	30.00 kW	1776 r/min	50.30 A	0.840	92.90 %	161.00 N·m	7.70
Y	--	60 Hz	460 V	30.00 kW	1777 r/min	48.60 A	0.830	93.20 %	161.00 N·m	8.30
Connection Configuration										Y
Temperature Class Default										--
Input Voltage (U <sub>in</sub> )										400 V
Frequency (f)										50 Hz
Output Power										30 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2 Full Load (100%) 92.3 % Partial Load (75%) 93.5 % Partial Load (50%) 93.5 %
IE Class Data (60 Hz)										IE Class IE1 Full Load (100%) 92.9 % Partial Load (75%) 93.6 % Partial Load (50%) 93.2 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										4
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Material	Aluminum
Frame Size	180
Bearing	6310-2Z/C3
Bearing NDE	6209-2Z/C3
IM Class	IMB35 IM2001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	726 mm
Product Net Height	405 mm

Product Net Width	354 mm
Product Net Weight	177 kg
Gross Weight	187 kg

Environmental

SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)
------	---

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

