



PRODUCT-DETAILS

3GAA188125-ADG

No Description Available

"No longer for sale" replaced by 3GAA188418-

General Information	
Product ID	3GAA188125-ADG
ABB Type Designation	M3AA 180MLA 2/4
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M3AA 180MLA 2/4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6310-2Z/C3
Bearing NDE	6209-2Z/C3
Country of Origin	Sweden (SE)
Customs Tariff Number	85015230
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Torque	IS/IN
YY	--	50 Hz	400 V	21.50 kW	2953 r/min	38.00 A	0.900	70.00 N·m	7.80
Y	--	50 Hz	400 V	4.70 kW	1478 r/min	10.70 A	0.710	30.00 N·m	6.10

Frame Material	Aluminum
Frame Size	180
Gross Weight	159 kg
IC Class	IC411
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2
Number of Poles (Low)	4
Order Multiple	1 piece
Package Level 1 Units	0 pallet (lift)
Product Name	3-Phase squirrel cage motor

Product Net Weight	149 kg
Product Type	3AA2__M3AA_IE2_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA188418-ADG
Selling Unit of Measure	piece
Service Factor	0.00
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	Yes
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D