

PRODUCT-DETAILS

# 3GAA183410-ASK

## IE3 Premium Efficiency Aluminum Motors, 15 kW, 400 V (3GAA183410-ASK)



General Information	
Product ID	3GAA183410-ASK
ABB Type Designation	M3AA 180MLA 6
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 15 kW, 400 V (3GAA183410-ASK)

Ordering	
ABB Type Designation	M3AA 180MLA 6
Invoice Description	M3AA 180MLA 6
Product Name	3-Phase squirrel cage motor
Product Type	3AA3_M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA183051-ASK
Stocked At (Warehouses)	Menden, Germany

Medium Description	15kW, 6 Poles, Frame Size 180, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA183410-ASK)
Short Description	15kW, 6P, Frame Size 180, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	15.00 kW	987 r/min	30.40 A	0.770	91.20 %	146.00 N·m	5.50
D	--	50 Hz	230 V	15.00 kW	987 r/min	53.20 A	0.770	91.20 %	146.00 N·m	5.50
Y	--	50 Hz	380 V	15.00 kW	985 r/min	31.30 A	0.790	91.20 %	146.00 N·m	5.00
D	--	50 Hz	220 V	15.00 kW	985 r/min	54.40 A	0.790	91.20 %	146.00 N·m	5.00
Y	--	50 Hz	415 V	15.00 kW	988 r/min	30.10 A	0.750	91.20 %	146.00 N·m	5.80
Y	--	60 Hz	460 V	15.00 kW	1189 r/min	27.10 A	0.750	92.30 %	120.00 N·m	6.00

Connection Configuration	Y
Temperature Class Default	--
Input Voltage (U <sub>in</sub> )	400 V
Frequency (f)	50 Hz
Output Power	15 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 91.2 % Partial Load (75%) 91.3 % Partial Load (50%) 90.0 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 92.3 % Partial Load (75%) 92.0 % Partial Load (50%) 90.5 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	180
Bearing	6310-2Z/C3
Bearing NDE	6209-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions	
Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	726 mm
Product Net Height	405 mm
Product Net Width	341 mm
Product Net Weight	175 kg
Gross Weight	185 kg

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

